e2v

To be read in conjunction with "Introduction to Pellistor Gas Sensors" and Pellistor Application Notes 1, 2, 3, 4, 6 and 7.

INTRODUCTION

The VQ1 consists of two matched elements which are used for the detection of combustible gases, particularly methane in air mixtures in concentrations from 0.1% upwards. There is no interference from water vapour or carbon dioxide. Using the recommended bridge circuit (see below) and the mounting arrangement shown on page 2, the minimum sensitivity is 20 mV/% methane.

GENERAL DATA

Electrical

The information given below relates to the VQ1 operating in the recommended circuit shown.

Operation (see note 1)
Bridge supply \ldots \ldots \ldots \ldots \ldots \ldots $2.0 \pm 0.1 $ V
Bridge power consumption 0.75 W max
Minimum sensitivity (see note 2) 20 mV/% methane
Linearity linear up to 3% methane
Response time to register $1^{1}/_{4}\%$ in a $2^{1}/_{2}\%$
concentration (see notes 2 and 3)

Mechanical

Mou	nting													see page 2
Outli	ne .													see page 2
Shoo	ck test							25	0 g	, 5	blc	ws	in	each plane
Vibra	ation t	est			2	20 g	, 2	24 c	ycl	es	froi	m 1	00	to 3200 Hz

Combustible Gas Detector Elements

MARKING

Each element carries a serial number sleeve, fitted to one of the flexible leads. The number is in standard colour code (see table), reading from the base towards the free end of the lead.

VQ1

Colour Code

Black	0	Yellow	4	Grey	8
Brown	1	Green	5	White	9
Red	2	Blue	6		
Orange	3	Violet	7		


The detector bead is dark in colour and has a red sleeve on the second lead. This sleeve carries a letter code which, together with the serial number, fully identifies a pair of elements.

The compensator bead is white and carries a black sleeve on the second lead.

NOTES

- 1. Operation may be under either direct flow or diffusion conditions in appropriate mountings (see page 2).
- 2. With open-circuit conditions at the bridge output.
- 3. The response time is a function of the type of mounting used.
- 4. If the VQ1 is exposed to greater than 5% methane concentration, the calibration of the instrument should be checked.
- 5. The elements are supplied as a matched pair with a trimming resistor R of the correct value which is between 39 and 120 Ω . The trimming resistor is to be connected across the compensator element as shown below.
- The elements must be protected from certain organic and silicone vapours by suitable filtering, and caution should be exercised when operating in close proximity to hot, oily machinery.

BRIDGE CIRCUIT




e2v technologies (uk) limited, Waterhouse Lane, Chelmsford, Essex CM1 2QU, UK Telephone: +44 (0)1245 493493 Facsimile: +44 (0)1245 492492 e-mail: enquiries@e2v.com Internet: www.e2v.com Holding Company: e2v technologies plc

e2v technologies inc. 4 Westchester Plaza, PO Box 1482, Elmsford, NY10523-1482 USA Telephone: (914) 592-6050 Facsimile: (914) 592-5148 e-mail: enquiries@e2vtechnologies.us

© e2v techno的時間移動化を出れの7/www.sensor-ic.com/ TEL: 0755-83376489 FAX:0755-83376182 E-MAIL:szAs2204AQ3.Issue 4, March 2007

OUTLINE (All dimensions without limits are nominal)




Ref	Inches	Millimetres
A	0.435 ± 0.010	11.05 ± 0.25
В	0.240 ± 0.010	6.10 ± 0.25
С	0.140 ± 0.005	3.56 ± 0.13
D	2.500 min	63.5 min
Е	0.040	1.02
F	0.230 ± 0.020	5.84 ± 0.51
G	0.323 max	8.20 max
Н	0.375	9.53
J	0.060	1.52

Millimetre dimensions have been derived from inches.


Note No bends may be made in this length.

RECOMMENDED MOUNTING ARRANGEMENTS



Ref	Inches	Millimetres
AA	0.750 max	19.05 max
AB	0.375 ± 0.005	9.53 ± 0.13
AC	0.328 ± 0.005	8.33 ± 0.13
AD	0.323 min	8.20 min
AE	0.750 max	19.05 max
AF	0.375 ± 0.005	9.53 ± 0.13
AG	0.323 min	8.20 min

Millimetre dimensions have been derived from inches.



Whilst e2v technologies has taken care to ensure the accuracy of the information contained herein it accepts no responsibility for the consequences of any use thereof and also reserves the right to change the specification of goods without notice. e2v technologies accepts no liability beyond that set out in its standard conditions of sale in respect of infringement of third party patents arising from the use of tubes or other devices in accordance with information contained herein.