

Multi-wavelength Lamps


Wavelengths can be individually driven or powered simultaneously for a broadband light source




T0-3 Package—Up to 8 wavelengths




T0-5 Package—Up to 12 wavelengths



LCC—Up to 24 wavelengths



T0-3 Package 8 wavelengths individually addressable



T0-3 Package 8 wavelengths broadband light source

Ideal Light source for UV Spectroscopy Application

- Instant on/off
Fast switching ~2 nanoseconds
Eliminates need for choppers
- Fully customizable
Select wavelengths for your application
From 240nm to 355nm (longer wavelengths available on request)
- Long Life
- Robust and Compact
Ideal for portable systems

